

LIGHTWEIGHT, PORTABLE THERAPY UNIT

- Easy to use full color LCD screen with touch-screen controls
- Single-touch therapy on/off
- Intuitive menus simplify therapy programming and operation
- Quick release, multi-orientational 300ml canister
- Discreet carrying case provided for ambulatory use

SENSAT.R.A.C.™ TECHNOLOGY

- Proprietary technology monitors and maintains set negative pressure at the wound site
- Designed to help reduce false alarms and tubing blocks
- Tubing and Pad designed with patient comfort in mind

SEAL CHECK™ FEATURE

- Provides instant feedback to help identify leaks
- Helps ensure seals
- Easy troubleshooting for patients; can help reduce unscheduled caregiver visits

THERAPY HISTORY REPORT

- Allows clinicians to monitor and track therapy settings, alarm history, therapy dates and times, dressing and canister changes and records the number of pieces of foam used

SETTINGS GUIDE

- Aligned with V.A.C.® Therapy Clinical Guidelines
- Optional preset therapy settings by wound type eases setup
- Step-by-step guide simplifies setup for infrequent users



SPECIFICATIONS:

ACTIV.A.C.™ Negative Pressure Wound Therapy System: P/N 340000

Weight:2.4 lbs (1.08 kg) with an empty canister
 Dimensions:7.6" W x 6" H x 2.5" D (19.3 x 15.2 x 6.4cm)
 Battery Type:.....Lithium ion rechargeable battery
 Battery Life:14 hour average, depending on settings
 Recharging Time:.....6 hours max
 Canister Size:300ml
 Therapy Delivery Modes:Continuous or Intermittent
 Intensity Settings:Low, Medium, High
 Therapy Pressure Options:-25mmHg to -200mmHg (-3.3 kPa to -26.6 kPa)

ELECTRICAL DATA

External Power Supply Input:100-240 VAC .72 A @ 115 VAC 47-63 Hz
 External Power Supply Output:12 V, 3.3 A
 Patient & Enclosure Leakage Current:.....<100 Microamps

IEC CLASSIFICATION

- Type B, Applied Part Class II IPX0
- Equipment not suitable for use in presence of flammable anesthetic mixture with air, oxygen or nitrous oxide

STORAGE CONDITIONS

Temperature Range:.....-4°F (-20°C) to 140°F (60°C)
 Relative Humidity Range:0-95% non-condensing

OPERATING CONDITIONS

Temperature Range:.....41°F (5°C) to 104°F (40°C)
 Relative Humidity Range:0-95% non-condensing
 Altitude Range:0 to 14,000 feet (0 to 4267 m)
 Optimum Performance:.....0 to 8,000 feet (0 to 2438 m)

NOTE: Specific indications, contraindications, warnings, precautions and safety information exist for KCI products and therapies. Please consult product instructions for use prior to application. Rx only.

©2009-2016 KCI Licensing, Inc. All rights reserved. All trademarks designated herein, unless otherwise noted, are proprietary to KCI Licensing, Inc.
 DSL#16-0372.US (Rev. 4/16)